



www.ditex.it

#9655304880

EQUIPMENT #1	CRI 1000 S
EQUIPMENT #2	CRI 1000 NEW STYLE
EQUIPMENT #3	DX73615
ADAPTOR	

DELIVERY PIPE	DX73260
BACKLEAKAGE PIPE	DX73262
CURRENT PROFILE	3
INJ TYPE	PIEZO

WORKSHOP	Relais Herouville
CUSTOMER #ID	02.03.2023
EMAIL	sa.relais.herouville@wanadoo.fr
ORDER #ID	

2010 MAY

DX73780	MIN	MAX
RESISTANCE Ω		
INDUCTANCE μH		
CAPACITANCE μF		

INJ 1	INJ 2	INJ 3	INJ 4	INJ 5	INJ 6

#	RAIL PRESSURE	CRI 1000 S	Q_MIN cm <sup>3</sup> /1000 strokes	Q_MAX cm <sup>3</sup> /1000 strokes	BL cm <sup>3</sup> /1000 strokes
A	1500	pos 6	3 min		
B	1550	OFF	#####	#####	≤30
1	1500	pos 5	30,1	34,0	65
2	220	pos 4	4,4	8,2	<10
3	1150	pos 5	27,9	30,9	
4	1000	pos 4	20,3	24,0	
5	850	pos 1	5,3	7,2	
6	220	pos 4	4,4	8,2	<10
7					

ISO 4113 40°C ± 2°C

Q	BL	Q	BL	Q	BL	Q	BL	Q	BL	Q	BL
	11		13		15		15				
28	30	26	31	27	36	29	40				
5,6	5,6	5,2	5,8	6,4	6,4	5,4	6,4				
27,4		16,8		26		22,2					
21		20,4		20		19,8					
4,6		2,9		3,5		4,2					
5,4	6	5,8	6,4	6,6	7	6	7				

28/10/2011-9:21 DITEX TECHNOLOGIES reserves the right to change, modify and/or withdraw the information in this TEST DATA at any time without notice. Therefore it is recommended to order latest test plan from